

Blanking plug QBC-3/16H-U

Part number: 564785

FESTO



Data sheet

Feature	Value
Size	Standard
Type code	QBC
Mounting position	Any
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.951 bar ... 9.997 bar
Temperature-dependent operating pressure	-0.951 bar ... 9.997 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	0 °C ... 60 °C
Product weight	0.992 g
Pneumatic connection 1	Push-in sleeve QS-3/16"
Note on materials	Contains paint-wetting impairment substances RoHS-compliant