

Plug NECU-S-M8G3-HX-Q3

Part number: 564945

FESTO



Data sheet

Feature	Value
Type code	NECU
Based on norm	EN 61076-2-104 EN 61984
Certification	c UL us - Recognized (OL)
Contact durability	3
Product weight	7.8 g
Electrical connection	3-pin M8x1 Straight plug/insulation displacement connector
DC operating voltage range	0 V ... 32 V
Operating voltage range AC	0 V ... 32 V
Current rating at 40°C	2 A
Surge resistance	0.8 kV
Approved cable diameter	2.1 mm ... 3.5 mm
Individual wire diameter	≥0.05 mm
Wire diameter	0.6 mm ... 1 mm
Connection cross section	0.1 mm ² ... 0.14 mm ²
Degree of protection	IP65 IP67
Ambient temperature	-25 °C ... 85 °C
Note on materials	Free of copper and PTFE RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	1 - Low corrosion stress
Housing material	PA Die-cast zinc Nickel-plated
Material of screw-type lock	Brass, nickel-plated
Seals material	FPM PUR
Material of pin contacts	Gold-plated
Permissible insulating sheath	PVC PP