

Push-in T-fitting CRQST-1/8-5/32-U

Part number: 565334

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	2.997 mm
Type code	CRQST
Mounting position	Any
Design	T-shape
Pack size	1
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.951 bar ... 14.003 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C ... 150 °C
Max. tightening torque	12 Nm
Product weight	18.598 g
Usable connector cables	PFAN
Type of mounting	External hexagon 15/32
Pneumatic connection 1	Male thread 1/8 NPTF
Pneumatic connection 2	for pneumatic tubing outside diameter 5/32"
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Housing material	High-alloy stainless steel
Releasing ring material	High-alloy stainless steel
Material of tubing seal	FPM
Material of tube retaining claw	High-alloy stainless steel