

Cover plate VABB-L1-10-W

Part number: 566495

FESTO



Data sheet

Feature	Value
Width dimension	10.5 mm
Type code	VABB
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Certification	RCM compliance mark c UL us - Recognized (OL)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Product weight	24 g
Note on materials	RoHS-compliant
Cover plate material	PA