

Manifold rail VABM-L1-10S-G18-9

Part number: 566565

FESTO



Data sheet

Feature	Value
Width dimension	10.5 mm
Type code	VABM
Max. no. of valve positions	16
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Certification	RCM compliance mark c UL us - Recognized (OL)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Max. tightening torque for H-rail mounting:	1.5 Nm
Max. tightening torque for valve mounting	0.45 Nm
Max. tightening torque for wall mounting	3 Nm
Product weight	171 g
Pneumatic connection 1	G1/8
Pneumatic connection 3	G1/8
Note on materials	RoHS-compliant
Manifold rail material	Wrought aluminum alloy