

Electrical sub-base VAVE-L1-1H3-LR

Part number: 566717

FESTO



Data sheet

| Feature | Value |
|--|--|
| Type code | VAVE |
| Reverse polarity protection | for operating voltage |
| Additional functions | Spark suppression Holding current reduction |
| Signal status display | LED |
| Nominal operating voltage DC | 24 V |
| Surge resistance | 0.8 kV |
| Contamination level | 3 |
| Certification | RCM compliance mark |
| CE marking (see declaration of conformity) | As per EU EMC directive |
| Corrosion resistance class (CRC) | 0 - No corrosion stress |
| Degree of protection | IP40 |
| Ambient temperature | -5 °C ... 60 °C |
| Mounting position | Any |
| Product weight | 1.5 g |
| Electrical connection | 2-pin Socket |
| Protective earth connection | Not available |
| Type of mounting | Clip |
| Housing colour | Black |
| Note on materials | RoHS-compliant |
| Housing material | PA |