

Electrical sub-base VAVE-L1-1L1-LR

Part number: 566726

FESTO



Data sheet

Feature	Value
Type code	VAVE
Reverse polarity protection	for operating voltage
Additional functions	Spark suppression Holding current reduction
Signal status display	LED
Nominal operating voltage DC	24 V
Surge resistance	0.8 kV
Contamination level	3
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive
Corrosion resistance class (CRC)	0 - No corrosion stress
Degree of protection	IP40
Ambient temperature	-5 °C ... 60 °C
Mounting position	Any
Product weight	4.6 g
Connection cross section	0.14 mm ²
Electrical connection	Flying lead
Cable length	0.5 m
Protective earth connection	Not available
Type of mounting	Clip
Housing colour	Black
Note on materials	RoHS-compliant
Housing material	PA