

# Stroke reduction HGPL-HR-63

Part number: 567831

FESTO



## Data sheet

Feature	Value
Size	63
Adjustable end position range/length	40 mm
Type code	HGPL
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	5 °C ... 60 °C
Product weight	1060 g
Type of mounting	Screwed on to pneumatic gripper
Note on materials	Free of copper and PTFE RoHS-compliant
Plate material	Wrought aluminum alloy