

Plastic tubing PUN-H-5/32-BR-150-CB

Part number: 567994

FESTO



Data sheet

| Feature | Value |
|--|--|
| External-Ø inches | 5/32 |
| Bending radius relevant for flow rate | 15.85 mm |
| Min. bending radius | 6.096 mm |
| Type code | PUN-H |
| Tubing characteristics | Suitable for energy chains in applications with high cycle rates |
| Pneumatic tubing test conditions | Suitability for energy chains: >5 million cycles as per FN 942021 |
| Temperature-dependent operating pressure | -0.993 bar ... 9.997 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com |
| For use in the food industry | See supplementary material information |
| Ambient temperature | -35 °C ... 63 °C |
| Product weight by length | 0.09 kg/m |
| Pneumatic connection | For plug connection outside diameter 5/32" |
| Color | Brown |
| Shore hardness | D 52 +/-3 |
| Note on materials | Free of copper and PTFE RoHS-compliant |
| Material of pneumatic tubing | TPE-U(PU) |