

Plastic tubing PLN-3/8-NT-150-CB

Part number: 569901

FESTO



Data sheet

| Feature | Value |
|--|--|
| External-Ø inches | 3/8 |
| Bending radius relevant for flow rate | 56.998 mm |
| Min. bending radius | 35.052 mm |
| Type code | PLN |
| Temperature-dependent operating pressure | -0.993 bar ... 13.996 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:-:-] Water as per manufacturer's declaration at www.festo.com |
| For use in the food industry | See supplementary material information |
| Ambient temperature | -30 °C ... 80 °C |
| Product weight by length | 0.403 kg/m |
| Pneumatic connection | For plug connection outside diameter 3/8" |
| Color | Natural |
| Shore hardness | D 52 +/-3 |
| Note on materials | Free of copper and PTFE RoHS-compliant |
| Material of pneumatic tubing | PE |