

# Plastic tubing PLN-1/4-BL-150-CB

Part number: 569915

FESTO



## Data sheet

Feature	Value
External-Ø inches	1/4
Bending radius relevant for flow rate	32.004 mm
Min. bending radius	11.887 mm
Type code	PLN
Temperature-dependent operating pressure	-0.993 bar ... 13.996 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-:] Water as per manufacturer's declaration at <a href="http://www.festo.com">www.festo.com</a>
For use in the food industry	See supplementary material information
Ambient temperature	-30 °C ... 80 °C
Product weight by length	0.18 kg/m
Pneumatic connection	For plug connection outside diameter 1/4"
Color	Blue
Shore hardness	D 52 +/-3
Note on materials	Free of copper and PTFE RoHS-compliant
Material of pneumatic tubing	PE