

Adapter VAVE-C8-1R8

Part number: 571686

FESTO



Data sheet

Feature	Value
Type code	VAVE
Signal status display	LED
Nominal operating voltage DC	24 V
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-5 °C ... 60 °C
Mounting position	Any
Tightening torque	0.25 Nm
Product weight	3.5 g
Electrical connection	3-pin/2-pin M8 / - Plug/socket
Protective earth connection	Not available
Type of mounting	On air solenoid valve with M2 central screw
Note on materials	RoHS-compliant
Housing material	PA
Material of pin contacts	Bronze