

# Electrical sub-base VAVE-L1-1VK7-LP

Part number: 573942

FESTO



## Data sheet

Feature	Value
Type code	VAVE
Cable characteristic	for static applications
Reverse polarity protection	Bipolar
Additional functions	Spark suppression
Signal status display	LED
Nominal operating voltage DC	24 V 12 V
Surge resistance	0.8 kV
Contamination level	3
Corrosion resistance class (CRC)	0 - No corrosion stress
Degree of protection	IP65
Ambient temperature	-5 °C ... 60 °C
Mounting position	Any
Max. tightening torque	0.27 Nm
Min. cable bending radius	34 mm
Product weight	20 g
Electrical connection	2-pin/2-wire Angled socket/cable Rectangular design/open end
Cable design	2 x 0.25 mm <sup>2</sup>
Cable diameter	3.4 mm
Cable diameter tolerance	± 0.2 mm
Cable length	1 m
Protective earth connection	Not available
Type of mounting	On air solenoid valve with self-tapping screw
Housing colour	Black
Note on materials	RoHS-compliant
Housing material	PA
Material of cable sheath	TPV