

Electrical sub-base VAVE-L1-1K9-LR

Part number: 573948

FESTO



Data sheet

Feature	Value
Type code	VAVE
Cable characteristic	for static applications
Reverse polarity protection	Bipolar
Additional functions	Spark suppression Holding current reduction
Signal status display	LED
Nominal operating voltage DC	24 V
Surge resistance	0.8 kV
Contamination level	3
Certification	RCM compliance mark
CE marking (see declaration of conformity)	As per EU EMC directive
Corrosion resistance class (CRC)	0 - No corrosion stress
Degree of protection	IP65
Ambient temperature	-5 °C ... 60 °C
Mounting position	Any
Max. tightening torque	0.27 Nm
Min. cable bending radius	34 mm
Product weight	92 g
Electrical connection	2-pin/2-wire Angled socket/cable Rectangular design/open end
Cable design	2 x 0.25 mm ²
Cable diameter	3.4 mm
Cable diameter tolerance	± 0.2 mm
Cable length	5 m
Protective earth connection	Not available
Type of mounting	On air solenoid valve with self-tapping screw
Housing colour	Black
Note on materials	RoHS-compliant
Housing material	PA
Material of cable sheath	TPV