


Connecting cable NEBV-C-S7WA44HS-K-10-N-LE36-S10

FESTO

Part number: 577378



Data sheet

Feature	Value
Type code	NEBV
Based on norm	DIN 47100
Cable designation	Without label holder
Contact durability	50
Product weight	1800 g
Electrical connection 1, function	Field device end
Electrical connection 1, design	Rectangular
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	44
Electrical connection 1, occupied pins/wires	36
Electrical connection 1, type of mounting	2x screw, 4-40 UNC With seal
Electrical connection for input 1, connection pattern	00995646
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	36
DC operating voltage range	0 V ... 30 V
Current rating at 40°C	0.86 A
Protective earth connection	Not available
Cable length	10 m
Cable characteristic	Standard
Bending radius, fixed cable installation	≥39 mm
Bending radius, flexible cable installation	≥115 mm
Cable diameter	9.6 mm
Cable diameter tolerance	± 0.2 mm
Cable design	36 x 0.25 mm ²
Nominal conductor cross section	0.25 mm ²
Degree of protection	IP65 IP67 IP69K
Note on degree of protection	In mounted state
Special features	Easy to clean
Ambient temperature	-5 °C ... 60 °C

Feature	Value
Ambient temperature with flexible cable installation	-5 °C ... 60 °C
Storage temperature	-20 °C ... 40 °C
Note on materials	RoHS-compliant
Contamination level	3
Corrosion resistance class (CRC)	3 - High corrosion stress
Material of cable sheath	PVC
Color cable sheath	Gray
Housing material	PA-reinforced
Housing colour	Gray
Material of screws	Stainless steel
Seals material	EPDM
Material of pin contacts	Bronze, gold-plated
Insulating sheath material	PVC