


# Manifold rail VABM-L1-18G-G38-12-G

Part number: 8004906

FESTO



## Data sheet

Feature	Value
Width dimension	19 mm
Type code	VABM
Mounting position	Any
Max. no. of valve positions	12
Certification	c UL us - Recognized (OL)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-20 °C ... 60 °C
Product weight	3061 g
Pilot air port 12/14	G1/8
Pilot exhaust air port 82/84	G1/8
Pneumatic connection 1	G3/8
Pneumatic connection 3	G3/8
Pneumatic connection 5	G3/8
Note on materials	RoHS-compliant
Manifold rail material	Wrought aluminum alloy