

Solenoid coil VACS-C-C1-3W

Part number: 8025338

FESTO



Data sheet

Feature	Value
Type code	VACS
Mounting position	Any
Duty cycle	100%
Insulation class	H
Coil characteristics	230/240 V AC: 50/60 Hz, initial power 3.0 VA, holding power 2.3 VA
Surge resistance	4 kV
Contamination level	3
Permissible voltage fluctuations	+/- 10 %
CE marking (see declaration of conformity)	As per EU low voltage directive
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Degree of protection	IP65
Ambient temperature	-10 °C ... 50 °C
Product weight	34.6 g
Electrical connection	Form C as per EN 175301-803
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Housing material	PA Steel
Solenoid coil material	Copper Steel Thermoplastic
Material of winding	Copper