

Common supply manifold VABM-B10-25-G12-7-P53

Part number: 8026224

FESTO



Data sheet

Feature	Value
Width dimension	27.5 mm
Type code	VABM
Mounting position	Any
Max. no. of valve positions	7
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Product weight	668 g
Type of mounting	With mounting bracket
Pneumatic connection 1	G1/2
Note on materials	RoHS-compliant
Manifold rail material	Wrought aluminum alloy