

Common supply manifold VABM-B10-25-N12-8-P53

Part number: 8026234

FESTO



Data sheet

| Feature | Value |
|----------------------------------|-------------------------------|
| Width dimension | 27.5 mm |
| Type code | VABM |
| Mounting position | Any |
| Max. no. of valve positions | 8 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Product weight | 750 g |
| Type of mounting | With mounting bracket |
| Pneumatic connection 1 | 1/2 NPT |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |