

Connection block VABM-B10-30S-G12-6-P3

Part number: 8026417

FESTO



Data sheet

| Feature | Value |
|----------------------------------|-------------------------------|
| Width dimension | 32 mm |
| Type code | VABM |
| Mounting position | Any |
| Max. no. of valve positions | 6 |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Product weight | 1533 g |
| Type of mounting | With through-hole |
| Pneumatic connection 1 | G1/2 |
| Pneumatic connection 3 | G1/2 |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy |