


# Supply plate VABF-B10-30-P1A4-G38-P3

Part number: 8026435

FESTO



## Data sheet

Feature	Value
Type code	VABF
Operating pressure	-0.9 bar ... 10 bar
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Max. tightening torque	6 Nm
Product weight	121 g
Type of mounting	With through-hole
Pneumatic connection 1	G3/8
Note on materials	RoHS-compliant
Supply plate material	Die-cast aluminum