

Reducing nipple NPFC-R-G18-M5-FM

Part number: 8030314

FESTO



Data sheet

| Feature | Value |
|----------------------------------|--|
| Type code | NPFC |
| Threaded fitting material | Brass, nickel-plated |
| Pack size | 10 |
| Operating pressure | -0.95 bar ... 50 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [:-:-] |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Ambient temperature | -20 °C ... 150 °C |
| Product weight | 9.3 g |
| Pneumatic connection 1 | G1/8 |
| Pneumatic connection 2 | M5 |
| Note on materials | RoHS-compliant |