

Solenoid coil VACF-B-B2-5

Part number: 8030801

FESTO



Data sheet

Feature	Value
Type code	VACF
Mounting position	Any
Duty cycle	100%
Insulation class	H
Coil characteristics	12 V DC: 3.4 W
Permissible voltage fluctuations	+/- 10 %
Certification	c UL us - Recognized (OL)
Maritime classification	See certificate
Certificate issuing authority	DNVGL-TAA000011J
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	-20 °C ... 50 °C
Degree of protection	IP65
Ambient temperature	-20 °C ... 50 °C
Product weight	55.6 g
Electrical connection	Form B As per industrial standard (11 mm)
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Housing material	PA Steel
Solenoid coil material	Copper Steel Thermoplastic
Material of winding	Copper