

Individual subbase VABS-S1-2S-G12

Part number: 8032644

FESTO



Data sheet

Feature	Value
Width	58 mm
Type code	VABS
Based on norm	ISO 5599-1
Actuation type	Electrical
Sealing principle	Soft
Mounting position	Any
Operating pressure	0 bar ... 16 bar
Pilot pressure	0 bar ... 10 bar
Suitability for vacuum	yes
CE marking (see declaration of conformity)	As per EU low voltage directive
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
Storage temperature	-20 °C ... 60 °C
Temperature of medium	-10 °C ... 60 °C
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Ambient temperature	-10 °C ... 60 °C
Product weight	380 g
Type of mounting	with through-hole for M6 screw
Pneumatic connection 1	G1/2
Pneumatic connection 2	G1/2
Pneumatic connection 3	G1/2
Pneumatic connection 4	G1/2
Pneumatic connection 5	G1/2
Note on materials	RoHS-compliant
Material of sub-base	Die-cast aluminum