

Quick coupling socket NPHS-D6-P-G12F

Part number: 8059273

FESTO



Data sheet

Feature	Value
Type code	NPHS
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Standard nominal flow rate	1950 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Product weight	122 g
Pneumatic connection 1	Internal thread G1/2
Note on materials	RoHS-compliant