

Plastic tubing PTFEN-6X1-NT-100

Part number: 8061172

FESTO



Data sheet

Feature	Value
Outside diameter	6 mm
Bending radius relevant for flow rate	40 mm
Inside diameter	4 mm
Min. bending radius	38 mm
Type code	PTFEN
Temperature-dependent operating pressure	-0.95 bar ... 15 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Material fire test	UL94 V-0
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C ... 150 °C
Product weight by length	0.034 kg/m
Pneumatic connection	For plug connection outside diameter 6 mm For barbed fitting outside diameter 6 mm with union nut For barbed fitting, inside diameter 4 mm, with union nut For barbed fitting, inside diameter 4 mm
Color	Natural
Shore hardness	D 55 +/-5
Note on materials	RoHS-compliant
Material of pneumatic tubing	PTFE