

Plastic tubing PTFEN-10X1,5-NT-300

Part number: 8061180

FESTO



Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	100 mm
Inside diameter	7 mm
Min. bending radius	70 mm
Type code	PTFEN
Temperature-dependent operating pressure	-0.95 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Material fire test	UL94 V-0
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C ... 150 °C
Product weight by length	0.086 kg/m
Pneumatic connection	For plug connection outside diameter 10 mm For barbed fitting outside diameter 10 mm with union nut
Color	Natural
Shore hardness	D 55 +/-5
Note on materials	RoHS-compliant
Material of pneumatic tubing	PTFE