

# Plastic tubing PTFEN-1/2-NT-150

Part number: 8061183

FESTO



## Data sheet

Feature	Value
Outside diameter	12.7 mm
Bending radius relevant for flow rate	120 mm
Inside diameter	8.5 mm
Min. bending radius	81 mm
Type code	PTFEN
Temperature-dependent operating pressure	-0.95 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Material fire test	UL94 V-0
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C ... 150 °C
Product weight by length	0.153 kg/m
Pneumatic connection	For plug connection outside diameter 1/2"
Color	Natural
Shore hardness	D 55 +/-5
Note on materials	RoHS-compliant
Material of pneumatic tubing	PTFE