

Plastic tubing PTFEN-5/32-NT-300

Part number: 8063350

FESTO



Data sheet

Feature	Value
Outside diameter	3.97 mm
Bending radius relevant for flow rate	32 mm
Inside diameter	2.9 mm
Min. bending radius	32 mm
Type code	PTFEN
Temperature-dependent operating pressure	-0.95 bar ... 12 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Material fire test	UL94 V-0
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C ... 150 °C
Product weight by length	0.013 kg/m
Pneumatic connection	For plug connection outside diameter 5/32"
Color	Natural
Shore hardness	D 55 +/-5
Note on materials	RoHS-compliant
Material of pneumatic tubing	PTFE