

Manifold block VABS-P4-10S-G14

Part number: 8087327

FESTO



Data sheet

Feature	Value
Width	21 mm
Type code	VABS
Mounting position	Any
Special features	Oxygen-compatible as per DIN EN 1797
Structural design	Connection direction at side
Max. no. of valve positions	1
Operating pressure	0 bar ... 8 bar
Operating medium	Inert gas Air Oxygen
Information on operating and pilot media	Operation with oil lubrication not possible Maximum particle size 10 µm
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Storage temperature	-40 °C ... 80 °C
Temperature of medium	5 °C ... 50 °C
Ambient temperature	5 °C ... 50 °C
Product weight	70 g
Type of mounting	With through-hole
Pneumatic connection 1	G1/4
Pneumatic connection 2	G1/4
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Material of sub-base	Wrought aluminum alloy, anodized