

Plastic-coated metal tube PM-4

Part number: 9084

FESTO



Data sheet

Feature	Value
Outside diameter	6 mm
Bending radius relevant for flow rate	19 mm
Inside diameter	3.92 mm
Type code	PM
Temperature-dependent operating pressure	-0.95 bar ... 30 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Ambient temperature	-29 °C ... 65 °C
Product weight by length	0.024 kg/m
Color	Black
Note on materials	Free of copper and PTFE RoHS-compliant
Material of pneumatic tubing	Wrought aluminum alloy PE