


Flow control/muffler GRU-3/4-B

Part number: 9520

FESTO



Data sheet

Feature	Value
Type code	GRU
Valve function	Sound pressure flow control function
Selection of additional function	With pneumatic muffler
Pneumatic connection 1	G3/4
Adjusting element	Slotted screw
Type of mounting	Screw-in
Standard flow rate 6->0 bar	0 l/min ... 8000 l/min
Ambient temperature	-10 °C ... 70 °C
Housing material	Aluminum
Mounting position	Any
Symbol	00991451
Operating pressure for entire temperature range	0 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Temperature of medium	-10 °C ... 70 °C
Product weight	170 g
Cushioning insert material	PE
Material of screwed trunnion	Die-cast aluminum
Note on materials	RoHS-compliant
Material of adjusting screw	PA