

Ball valve QH-1

Part number: 9545

FESTO



Data sheet

Feature	Value
Type code	QH
Valve function	2/2 bistable
Pneumatic connection 1	G1
Pneumatic connection 2	G1
Actuation type	Manual
Type of mounting	Line installation
Standard nominal flow rate	33000 l/min
Nominal width	25 mm
Ambient temperature	-20 °C ... 180 °C
Housing material	Brass
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water
Sealing principle	Soft

Feature	Value
Structural design	Ball valve
Symbol	00991458
Nominal pressure of fitting PN	30
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)