


Short pulse valve VLK-3-PK-3

Part number: 9639

FESTO



Data sheet

Feature	Value
Nominal width	2.5 mm
Type code	VLK
Symbol	00992823
Operating pressure	2.5 bar ... 8 bar
Standard nominal flow rate	90 l/min
Explosion prevention and protection	Observe the information on the certificate Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Ambient temperature	-10 °C ... 60 °C
Product weight	170 g
Type of mounting	On mounting frame
Seals material	TPE-U(PU)
Housing material	Die-cast zinc