



Cut

Abrasion Protection



Medium Duty

## Versatile industrial gloves, combining cut protection, advanced durability and dexterity

- **Heightened protection:** HyFlex® 11-644 cut-resistant gloves' INTERCEPT™ Cut Resistance Technology helps them achieve EN ISO B/ANSI A2 laceration defenses
- **Enhanced durability:** These abrasion-resistant gloves' polyurethane coating remains both maneuverable and hard-wearing over time
- **Improved ergonomics:** The 11-644 model's ergonomic fit and low palm weight makes it perfectly comfortable for highly precise operations
- **Genuine practicality:** HyFlex® 11-644 PPE gloves are also sold in vend pack form, for practical replenishment and re-application in real-world conditions



### Industries

- Automotive
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

### Applications

- Press shop operations
- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Seizing structural and body parts
- Inspection (picking, checking and marking)
- Feeding the press and removing spare parts from it
- Cutting glasses, sheets, panels

#### Key Features

- **INTERCEPT™ Cut Resistance Technology:** Preventing workplace injuries
- **Abrasion resistance:** Durable personal protection over long periods
- **Lightweight ergonomic fit:** Offering dexterity and all-day comfort

#### Performance Standards & Regulatory Compliance

##### REACH Compliant



#### Technologies



#### Specifications

BRAND   STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-644	<b>Finishing:</b> Palm Coated <b>Coating Material:</b> Polyurethane <b>Liner Material:</b> HPPE, Nylon, Spandex <b>Cuff Style:</b> Knitwrist	13	5, 6, 7, 8, 9, 10, 11, 12	207-277 mm; 8.14-10.90 inches	Grey	<ul style="list-style-type: none"> <li>• 12 pairs in a bag; 12 bags in a carton</li> </ul>

#### For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

##### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
 Riverside Business Park  
 Blvd International, 55  
 1070 Brussels, Belgium  
 T: +32 (0) 2 528 74 00  
 F: +32 (0) 2 528 74 01

##### North America Region

Ansell Healthcare Products LLC  
 111 Wood Avenue South,  
 Suite 210  
 Iselin, NJ 08830, USA  
 T: +1 800 800 0444  
 F: +1 800 800 0445

##### Australia

Ansell Limited  
 Level 3, 678 Victoria Street,  
 Richmond, Vic, 3121  
 Australia  
 T: +61 1800 337 041  
 F: +61 1800 803 578

##### Asia Pacific Region

Ansell Global Trading Center  
 (Malaysia) Sdn Bhd  
 Prima 6, Prima Avenue  
 Block 3512, Jaijan Teknokrat 6  
 T: +603 8310 6688  
 F: +603 8310 6699

##### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
 Blvd. Bernardo Quintana No. 7001-C,  
 Q7001 Torre II,  
 Suites 1304, 1305 y 1306,  
 Col. Centro Sur, c.p. 76079  
 Queretaro, Qro. Mexico  
 T: +52 442 248 1544 / 248 3133

##### Canada

Ansell Canada  
 105 Lauder  
 Cowansville, QC J2K 2K8  
 Canada  
 T: +1 800 363 8340  
 F: +1 800 267 3551