



Ironcat®

Premium Top Grain Goatskin Leather MIG Welder's Glove with Split Cowhide Back

- Top Grain Goatskin leather construction is the softest, most abrasion-resistant leather and is highly recommended for applications requiring tactile sensitivity
- Top Grain leather is smooth, provides durability and dexterity
- Gunn cut pattern delivers excellent durability, wear and comfort, especially for heavier gloves
- Split Cowhide leather back provides comfort, durability, excellent abrasion resistance, and breathability
- Straight thumb increases comfort in closed-fisted work
- Fleece Lined for additional heat protection
- Stitched with Kevlar® adding strength and burn resistance
- Tan 4" split cowhide extended cuff allows for easy on and off

Technical Data

Color	Brown
Sizes Available	M-XL
Packaging	Pair Tagged Retail Ready
Packed	6 Dozen/Case
Case Dimensions (in)	19.02 x 15.00 x 19.02
Case Weight (lbs)	43.48
Country of Origin	Pakistan
Hide	Top Grain Goatskin
Lining	Fleece Pile
Grade	Premium
Cuff	Gauntlet
Length	--
Palm	Leather
Back	Leather
Closure	Slip On
Thumb	Straight
Stitching	Kevlar
Construction	Cut-and-Sewn, Gunn Cut
Certifications	--
Product Circularity	--

Performance Data

PPE Category	--
ARC Rating	cal/cm2
ANSI Cut Level (2016)	--
ANSI Puncture Level	--

Care Instructions



Do Not Wash



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
6143/M	Brown	M	662909002624	20662909002628	10662909002621
6143/L	Brown	L	662909002631	20662909002635	10662909002638
6143/XL	Brown	XL	662909002648	20662909002642	10662909002645