

## Chemical gloves with added grip and extended safety cuffs, ideal for outdoor applications

- **Enhanced grip:** AlphaTec® 58-535B industrial gloves' ANSELL GRIP™ coating reduces the force needed to handle oily or wet parts
- **Elevated comfort:** Their black acrylic inner liner improves comfort and facilitates outdoor application
- **Advanced defenses:** AlphaTec® 58-535B safety gloves boast a bonded construction, with a coating polymer that doesn't penetrate the liner in manufacture, preventing liquid and chemical leakage
- **Improved durability:** They also possess ANSI/EN-compliant abrasion resistance
- **Specialized protection:** In addition to chemical protection, they satisfy EN 407 contact heat level 1, preventing workplace injuries
- **Augmented dexterity:** AlphaTec® 58-535B PPE gloves' lightweight 7-gauge design offers greater dexterity and flexibility



### Industries

- Automotive
- Automotive Aftermarket
- Machinery and Equipment
- Metal fabrication
- Chemical
- Agriculture
- Emergency Medical Services
- Food Processing
- Oil and gas

### Applications

- Metalworking & assembly operations
- Body painting including surface inspection
- Applying sealers, touching up
- Changing tools and dies
- Handling application & cleaning tools
- Warehousing of raw materials
- Loading and unloading trucks and vehicles
- Filling, blending and charging of raw materials
- Transferring liquids and solids
- Loading and unloading of process equipment
- Transferring liquids and solids between vessels and tanks and process equipment
- Supervision of running operation
- Handling outgoing goods: cans, vessels, bulkpack and cartons
- Opening furnaces draining pumps valves or lines and crackers BTX process

# AlphaTec®

ADVANCED CHEMICAL PROTECTION

## 58-535B

Unique combination of grip and chemical resistance


### Key Features

- **ANSELL GRIP™ coating:** Gripping wet or oily parts requires less force
- **Black acrylic liner:** Comfort guaranteed, perfect for outdoor usage
- **Bonded construction:** Zero liner penetration and enhanced dexterity

### Technologies



### Performance Standards



### Specifications

BRAND   STYLE	DESCRIPTION	GAUGE	SIZE	LENGTH	COLOR	PACKAGE
AlphaTec® 58-535B	Acrylic, Nitrile, ANSELL GRIP™	7	7, 8, 9, 10, 11	340 mm / 13.4 inches	Grey	• 6 pairs/polybag; 12 polybags/ carton

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Canada

Ansell Canada Inc.  
105, rue Lauder  
Cowansville (Québec)  
J2K 2K8, Canada  
T: 1 800 363-8340  
F: 1 888 267-3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending:  
[www.ansell.com/patentmarking](http://www.ansell.com/patentmarking) © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

