



R-161

Touchscreen-compatible TPR and synthetic leather impact gloves, for comfort and usability



Impact

Abrasion Protection

Chemical Protection



Cut

Ergonomic Protection



Vibration



Light Duty

Touchscreen-compatible TPR impact gloves with synthetic leather, for comfort and usability

- **Specialized protection:** RINGERS® R161 impact gloves are developed with a patented flexible-knuckle TPR (thermoplastic rubber) design using F3 Technology™, for assured hand safety, dexterity and comfort
- **Improved durability and grip:** Their synthetic leather palm enhances grip performance and glove life, while a wraparound index finger offers resistance against wear and tear
- **Enhanced features:** These RINGERS® gloves' high-visibility external surface improves workplace safety, while touchscreen-compatible thumb tips, index and middle fingers make glove removal less frequent
- **Heightened defenses:** They feature a reinforced thumb, index, and middle finger, as well as a hook and loop rubber pull tab cuff for a secure fit, for safer impact protection gloves overall



Industries

- Manufacturing
- Mining
- Automotive
- Automotive Aftermarket
- Oil and gas
- Recycling and Waste Disposal
- Machinery and Equipment
- Metal fabrication
- Utilities
- Warehousing

Applications

- General Purpose Auto Aftermarket
- Handling structural and body components
- Body painting including surface inspection
- Applying sealers, touching up
- Body panel repair and replacement
- Oil, fluids and filter change
- Engine transmission and repair
- Tire rotation & changes
- Seizing structural and body parts
- Equipment maintenance and repair
- Assembly and disassembly of equipment
- Final assembly
- Final inspection
- Signalling/Positioning
- Operating of heavy machinery
- Hydraulic set and testing
- Loading and hauling



R-161

Touchscreen-compatible TPR and synthetic leather impact gloves, for comfort and usability

Key Features

- **Flexible-knuckle TPR design:** Finger and top-of-hand protection
- **Synthetic leather palm:** Enhanced durability and improved grip
- **Touchscreen compatibility:** Lesser glove removal, greater hand safety

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	COLOR	PACKAGE
RINGERS® R161	Liner Material: N/A Cuff Style: Adjustable		7, 8, 9, 10, 11, 12, 13	Hi Viz	5 pairs/bag, 10 bags/carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jalan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

