




ChemFR™

Treated PVC Two-Piece Acid Suit - 0.40 mm

- Special PVC layered material provides protection against various liquid splashes and incidental contact
- Vented cape back and underarm vents for a wide range of motion and comfort
- Four snap front closure
- Attached drawstring hood for secure fit
- Open wrist with adjustable snap closures
- Two flap pockets to secure valuables
- Overalls have open ankles with adjustable snap closures
- Adjustable suspenders with triangular buckles and studs
- Snap to fit sizing at the waist for a secure fit
- Not designed for use in an ARC flash or flash fire application
- Treated to provide limited flammability and is self-extinguishing (ASTM D6413 test method)
-  **WARNING:** Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Applications

- Road Work
- Municipal
- Shipyards
- Railyard
- Agriculture
- Plant Maintenance
- Not designed for use in an ARC flash or flash fire application



Technical Data

Color	Green
Sizes Available	M-4XL
Packaging	Bagged Each
Packed	10/Case
Case Dimensions (in)	20.25 x 14.50 x 6.75
Case Weight (lbs)	26.46
Country of Origin	China
Fabric	Polyester, PVC
Thickness	0.4 mm
Total Pockets	2
Pocket Type	Flap Pocket
Hood	Attached
Length	--
Closure	Snap
Construction	Water Resistant, Underarm Vents, Cape Vented Back
Certifications	ASTM D6413
Product Circularity	--

Care Instructions



Do Not Wash



SKU Information

SKU	COLOR	SIZE	UPC	UPC (INNER)	UPC (CASE)
4045/M	Green	M	662909404565		10662909404562
4045/L	Green	L	662909404510		10662909404517
4045/XL	Green	XL	662909404527		10662909404524
4045/XXL	Green	2XL	662909404534		10662909404531
4045/XXXL	Green	3XL	662909404541		10662909404548
4045/XXXXL	Green	4XL	662909404558		10662909404555