




LIFTING LUGS ARE DELIVERED UNASSEMBLED




FEET ARE DELIVERED UNASSEMBLED



T1 T2 T3.1 T3.2 T4.1 T4.2 locations on back side correspond to S1 S2 S3.1 S3.2 S4.1 S4.2 on front side

ALL DIMENSIONS IN MILLIMETERS



HEATING SURFACE
 NETWEIGHT 124.3 kg
 OPERATING WEIGHT
 PLATE MATERIAL Alloy 316
 PLATE GROUPING 1*64HR/1*65HB

SIDE	MEDIA	INLET	TEMP.	OUTLET	TEMP.	FLOW RATE	PRESSURE DROP	LIQUID VOL.
1								32 dm ³
2								30.6 dm ³

Note that all unique customer requirements (i.e tolerance) need to be verified thru Alfa Laval.

PRESSURE VESSEL APPROVAL UL/CRN

ACH-500EQ-130H Y55 (3287084415)

www.alfalaval.com

CUSTOMER NAME / REF. NO.

TOTAL LENGTH 453.8 mm
 TOTAL WIDTH 322.0 mm
 TOTAL HEIGHT 837.0 mm

COMPANY / REF.

3/15/2017
 REV 0