






	CEC Compliant	CEC Compliant	CEC Compliant	CEC Compliant
				
Model #	A019J-05KR	A016B1-06KR WIFI	A018C-08KR	A020A-10KR
Brand	JHS	JHS	JHS	JHS
UPC CODE	816621021788	816621021863	816621021856	816621021870
Performance				
ASHRAE BTU Cool	8,000	10,000	12,000	15,000
DOE SACC BTU	5,000	6,000	8,000	10,000
ASHRAE BTU Heat	NA	NA	NA	NA
min CEER	6.10	6.60	7.30	7.90
Pints/days	45	55	65	80
Target Sound Rating - High/Low Speed	52/50	52/50	52/50	52/50
CFM				
High	tbd	175	235	250
Med	tbd	155	215	220
Low	tbd	135	200	180
Operating Temperature Range F	68-80	68-80	68-80	68-80
Refrigerant Charge oz	9.9	12.0	14.0	17.3
Electrical				
Volts	115	115	115	115
Amps Cooling	6.9	8.0	9.9	11.4
Watts Cooling	780	900	1,120	1,300
Amps Heating	NA	NA	NA	NA
Watts Heating	NA	NA	NA	NA
Plug Capacity	120/15	120/15	120/15	120/15
Plug Type	5-15P	5-15P	5-15P	5-15P
Min Power Cord Length (ft)	6.0	6.0	6.0	6.0
LCDI /AFCI Power Cord	LCDI	LCDI	LCDI	LCDI
Exterior Appearance				
Color	Snow White	Snow White	Snow White	Snow White
Finish	Gloss	Gloss	Gloss	Gloss
Front Panel Logo	Pad Print	Pad Print	Badge	Badge
Front Panel Color	Snow White	Snow White	Snow White	Snow White
Top Decoration Chrome/no Chrome	No Separate Part	No Separate Part	Chrome	Chrome
Bottom Decoration Chrome Tape/no Chrome Tape	NA	NA	Chrome Tape	Chrome Tape
Back Panel Color	Snow White	Snow White	Snow White	Snow White
Side Panel Color	Snow White	Snow White	Snow White	Snow White
Control Panel	LED	LED	LED	LED
Airflow Configuration	Single Hose	Single Hose	Single Hose	Single Hose
Air Discharge	Front	Front	Top	Top
Air Direction - Up & Down (auto open louver)	Up & Down	Up & Down	Auto Louver	Auto Louver
Air Direction - Left & Right	No	No	No	No
Features				
Electronic Controls				
Controls	Tactile	Tactile	Cap Touch	Cap Touch

Unit LED display	Yes	YES	YES	YES
Auto-Restart	Yes	Yes	Yes	Yes
Digital Time/Temp Display	Yes	Yes	Yes	Yes
Fan Speeds - Cool/Fan/Heat	2/2 with Eco Mode	2/2 with Eco Mode	3/3	3/3
Thermostat	Thermistor	Thermistor	Thermistor	Thermistor
Dehumidify Function	Yes	Yes	Yes	Yes
On/Off Timer	24 Hour	24 Hour	24 Hour	24 Hour
Sleep Mode	No	No	No	No
Filter Check	No	No	No	No
Power Exhaust	No	No	No	No
Remote Control	Yes	Yes	Yes	Yes
Auto Mode	No	No	No	No
Wifi/Connected	No	YES	No	No
Filter Type	Permanent Mesh	Permanent Mesh	Permanent Mesh	Permanent Mesh
Filter Access	Easy Access	Easy Access	Easy Access	Easy Access
RoHS Compliant	Yes	Yes	Yes	Yes
Window Exhaust Kit	Yes	Yes	Yes	Yes
Window Kit min/max (in)	20" - 46"	20" - 46"	20" - 46"	20" - 46"
Minimum Window Opening	5.9	5.9	5.9	5.9
Exhaust Hose Length (ft)	5.0	5.0	5.0	5.0
Casters	Yes	Yes	Yes	Yes
Self Evaporative	Yes	Yes	Yes	Yes
Continuous Condensate Drain	Yes	Yes	Yes	Yes
Agency Approvals				
Performance Standard	ASHRAE 128/DOE SACC	ASHRAE 128/DOE SACC	ASHRAE 128/DOE SACC	ASHRAE 128/DOE SACC
Safety Approvals	cCSAus	cCSAus	cCSAus	ETL
Packaging				
Carton Design	Glossy Full Color	Glossy Full Color	Glossy Full Color	Glossy Full Color
Standard Packaging	ISTA 6A Amazon	ISTA 6A Amazon	ISTA 6A Amazon	ISTA 6A Amazon
Stack Height	3	3	3	3
Dimension, Weight & Shipping				
Unit Dimensions (in)				
Height	26.7	27.5	28.9	31.0
Width	12.0	13.9	16.7	18.7
Depth	13.0	13.3	14.7	15.0
Cu Ft	2.4	3.0	4.1	5.0
Carton Dimensions (in)				
Height	34.2	34.2	35.0	35.0
Width	13.7	15.8	18.8	18.8
Depth	14.9	15.1	15.6	15.6
Cu Ft	4.0	4.7	5.9	5.9
Weight lbs				
Net	45.7	49.7	57.1	62.5
Ship	54.1	59.6	70.1	75.5