

Keystone™

Window Air Conditioners



	KSTAW05CE	KSTAW06CE	KSTAW08CE	KSTAW10CE	KSTAW12CE
Capacity	5,000 Btu/h	6,000 Btu/h	8,000 Btu/h	10,000 Btu/h	12,000 Btu/h
Input	410 Watts	490 Watts	666 Watts	833 Watts	1000 Watts
Current	3.8 Amps	4.5 Amps	5.9 Amps	7.5 Amps	8.7 Amps
EER	12.2	12.2	12.0	12.0	12.0
Moisture Removal	1.3 pints/hr	1.5 pints/hr	2.1 pints/hr	2.3 pints/hr	2.5 pints/hr
Indoor dBA (Hi/Med/Lo)	56.5 / 53.9 / 50.5	56.4 / 54.1 / 51.9	60.4 / 58.5 / 56	___ / 59.5 / ___	60.5 / 59.3 / 57.7
Energy Star	No	No	No	No	No
Remote	LCD remote	LCD remote	LCD remote	LCD remote	LCD remote
Cooling Range	62°F ~ 90°F	62°F ~ 90°F	62°F ~ 90°F	62°F ~ 90°F	62°F ~ 90°F
Cooling Area	150 ft ²	250 ft ²	350 ft ²	450 ft ²	550 ft ²
Cooling Speeds	3	3	3	3	3
Fan Speeds	3	3	3	3	3
Power Cord Length	6.5 ft.	6.5 ft.	6.5ft.	6.5 ft.	6.5 ft.
Voltage	115V	115V	115V	115V	115V
UPC	192487238783	192487238790	192487238752	192487238820	192487238837
Included Items	air conditioner, remote, 2 AAA batteries, mesh filter, manual, 1 Yr parts & labor/5 Yr sealed system warranty	air conditioner, remote, 2 AAA batteries, mesh filter, manual, 1 Yr parts & labor/5 Yr sealed system warranty	air conditioner, remote, 2 AAA batteries, mesh filter, manual, 1 Yr parts & labor/5 Yr sealed system warranty	air conditioner, remote, 2 AAA batteries, mesh filter, manual, 1 Yr parts & labor/5 Yr sealed system warranty	air conditioner, remote, 2 AAA batteries, mesh filter, manual, 1 Yr parts & labor/5 Yr sealed system warranty