

Hermes

Biometric Auto Tracking Portable Security Camera



Fire Warning



Heat Mapping



Path Tracking



Facial
Recognition



Power Bank
Support



Military Encryption
Protection



240° Auto
Tracking



SPECIFICATION

Model (Hermes)	ACC1308E51WH
Encryptions Technologies	256-bit
Privacy Protection	Yes
Wireless	Embedded Wi-Fi (2.4G) 802.11 b/g/n
Multiple Wi-Fi Access Points	Connect up to 4 Wi-Fi Networks
Snapshot / Text / Offline Alert	Yes
10-Second Video Alert	Yes ¹
Audio	Built-in Speaker and Microphone
Real-Time Two-Way Communication	Yes
Greetings Function	Yes
Motion / Audio Detection	Yes
Fire Warning	Yes ²
Human Detection	Yes ²
Vehicle Detection	Yes ²
Face Detection	Yes
Pet Detection	Yes ²
Intruder Warning Light / Alarm	Yes
Multiple Viewers Support	Yes
Auto-Tracking Range	240°
Activity / Blockout Zones	Max: 4
Field of View (FOV)	85±5° (Diagonal)
Digital Zoom	4x

Pan	Pan: -80° ~ 80°
Frame Rate	1280 x 720 up to 30 fps
Resolution	1M Pixels FHD
Streaming Quality	Automatically Adjusted
Video Compression	H.264, MJPEG
Video Resolution	720p, 480p, 360p
Image Sensor	1/4" CMOS
IR / Flash LEDs	Flash LEDs: 1
MIMO Antenna	Embedded 1 x 1
Local Storage	Built-in 8GB memory
App Support	Amaryllo
Mobile OS Requirements	iOS: 10.0 and up / Android: 5.0 and up
Google Services Connection	Yes
PC Browser Support	Chrome / Firefox
Network Protocol	TCP/IP, UDP/IP, HTTP/HTTPS, DHCP, NTP, WPS
NAS Support	SMB / CIFS
Power Consumption	100V ~ 240V (5V / 2A DC)
Dimensions (H x W x D)	3.6 x .6 x 12.1 cm / 1.42" x 1.42" x 4.76"
Weight	107g / 3.77 oz
Ambient Operating Temperature	32°F ~ 95°F / 0°C ~ 35°C
Warranty	One-Year Part Warranty

¹ Feature available under our Basic plan and above.

² Features available under our Plus plans and above.

Hermes

ACCESSORIES



Mounting bracket



Power Adapter



USB Cable

