


# Apollo

Biometric Auto Tracking Pet Camera



## SPECIFICATION

Model (Apollo)	ACR1501R16WH
Encryptions Technologies	256-bit
Privacy Protection	Yes
Wireless	Embedded Wi-Fi (2.4G) 802.11 b/g/n
Multiple Wi-Fi Access Points	Connect up to 4 Wi-Fi Networks
Snapshot / Text / Offline Alert	Yes
10-Second Video Alert	Yes <sup>1</sup>
Audio	Built-in Speaker and Microphone
Real-Time Two-Way Communication	Yes
Greetings Function	Yes
Motion / Audio Detection	Yes
Fire Warning	Yes <sup>2</sup>
Human Detection	Yes <sup>2</sup>
Vehicle Detection	Yes <sup>2</sup>
Face Detection	Yes <sup>2</sup>
Pet Detection	Yes
Day / Night Vision	Yes
Intruder Warning Light / Alarm	Yes
Multiple Viewers Support	Yes
Auto-Tracking Range	360°
Activity / Blockout Zones	Max: 4
Field of View (FOV)	85±5° (Diagonal)

Digital Zoom	4x
Pan / Tilt	Pan: -170° ~ 170° / Tilt: -20° ~ 10°
Frame Rate	1920 x 1080 up to 30 fps
Resolution	2M Pixels FHD
Streaming Quality	Automatically Adjusted
Video Compression	H.264
Video Resolution	1080p, 720p, 480p, 360p
Image Sensor	1/2.7" CMOS
IR / Flash LEDs	IR LEDs: 8, Flash LEDs: 6
MIMO Antenna	Embedded 2 x 2
Local Storage	Supports up to 128GB Micro SD Card
App Support	Amaryllo
Mobile OS Requirements	iOS: 10.0 and up / Android: 5.0 and up
Google Services Connection	Yes
PC Browser Support	Chrome / Firefox
Network Protocol	TCP/IP, UDP/IP, HTTP/HTTPS, DHCP, NTP, WPS
NAS Support	SMB / CIFS
Power Consumption	100V ~ 240V (5V / 2A DC)
Dimensions (H x W x D)	9 x 9 x 10 cm / 3.54"x 3.54"x 3.94"
Weight	250 g / 0.55 lb
Ambient Operating Temperature	32°F ~ 95°F / 0°C ~ 35°C
Warranty	One-Year Part Warranty

<sup>1</sup> Feature available under our Basic plan and above.

<sup>2</sup> Features available under our Plus plans and above.

# Apollo Pet Edition

## ACCESSORIES



Width 3.94 inches (10 cm)

