








iBabiSmart

Capturing Every Milestone



-  Baby Cry Detection
-  360° Auto-Tracking
-  Baby Voice Detection
-  Military Encryption
-  Daily Report
-  Night Vision
-  Facial Recognition
-  1080P Full HD

SPECIFICATION

Model (iBabi Smart)	ACR1501R18WH	Digital Zoom	4x
Encryption Technology	256-bit	Pan / Tilt	Pan: -170° ~ 170° / Tilt: -20° ~ 10°
Privacy Protection	Yes	Frame Rate	1920 x 1080 up to 30 fps
Wireless	Embedded Wi-Fi (2.4G) 802.11 b/g/n	Resolution	2M Pixels FHD
Multiple Wi-Fi Access Points	Connect up to 4 Wi-Fi Networks	Streaming Quality	Automatically Adjusted
Snapshot / Text / Offline Alert	Yes	Video Compression	H.264, MJPEG
10-Second Video Alert	Yes ¹	Video Resolution	1080p, 720p, 480p, 360p
Audio	Built-in Speaker and Microphone	Image Sensor	1/2.7" CMOS
Real-Time Two-Way Communication	Yes	IR / Flash LEDs	IR LEDs: 8, Flash LEDs: 6
Greetings Function	Yes	MIMO Antenna	Embedded 2 x 2
Motion / Audio Detection	Yes	Local Storage	Supports up to 128GB Micro SD Card
Baby Cry Detection	Yes ¹	App Support	Amaryllo
Baby Voice Detection	Yes ¹	Mobile OS Requirements	iOS: 10.0 and up / Android: 5.0 and up
Lullaby Player	Yes ²	Google Services Connection	Yes
Face Detection	Yes	PC Browser Support	Chrome / Firefox
Daily Report	Yes	Network Protocol	TCP/IP, UDP/IP, HTTP/HTTPS, DHCP, NTP, WPS
Day / Night Vision	Yes	NAS Support	SMB / CIFS
Intruder Warning Light / Alarm	Yes	Power Consumption	100V ~ 240V (5V / 2A DC)
Multiple Viewers Support	Yes	Dimensions (H x W x D)	9 x 9 x 10 cm / 3.54"x 3.54"x 3.94"
Auto-Tracking Range	360°	Weight	250 g / 8.82 oz
Activity / Blockout Zones	Max: 4	Ambient Operating Temperature	32°F ~ 95°F / 0°C ~ 35°C
Field of View (FOV)	85±5° (Diagonal)	Warranty	One-Year Part Warranty

¹ Feature available under our 30-Day iBabi Plan and above.

² MicroSD Card is required.

iBabi Smart

ACCESSORIES

