

AR4

Biometric Outdoor Security Camera



Fire Warning



Heat Mapping



Path Tracking



Facial Recognition



Aluminum Material



Military Encryption Protection



Infrared Night Vision



Professional IP66 Grade

SPECIFICATION

Model (AR4)	ACR1501R4WH	Streaming Quality	Automatically Adjusted
Encryptions Technologies	256-bit	Video Compression	H.264, MJPEG
Privacy Protection	Yes	Video Resolution	1080p, 720p, 480p, 360p
Ethernet	RJ-45 (10/100BASE-T)	Image Sensor	1/2.7" CMOS
PoE Support	IEEE 802.3af/at	IR / Flash LEDs	IR LEDs: 36
RJ45 Cable	Cat. 5E UTP outside PE cover	Local Storage	Built-in 8GB memory
Snapshot / Text / Offline Alert	Yes	App Support	Soteria
Smart A.I. Features	Yes	Mobile OS Requirements	iOS: 9.0 and up / Android: 5.0 and up
Face / Motion / Audio Detection	Yes	Google Services Connection	Yes
Human Detection	Yes	PC Browser Support	Chrome / Firefox
Vehicle Detection	Yes	Network Protocol	TCP/IP, UDP/IP, HTTP/HTTPS, DHCP, NTP, WPS
Day / Night Vision	Yes	NAS Support	SMB / CIFS
Multiple Viewers Support	Yes	Power Consumption	100V ~ 240V (12V / 1A DC)
Activity / Blockout Zones	Max: 4	Dimensions (H x W x D)	6.8 x 6.8 x 21 cm / 2.68" x 2.68" x 8.27"
Field of View (FOV)	108°	Weight	370 g / 13.05 oz
Digital Zoom	4x	Ingress Protection Rating	IP66
Frame Rate	1920 x 1080 up to 30 fps	Ambient Operating Temperature	-40°F ~ 140°F / -40°C ~ 60°C
Resolution	2M pixels FHD	Warranty	One-Year Part Warranty

AR4

ACCESSORIES



DC 12V 1A adapter



Hex key

Screw anchor



Screw

