

Zeus

Biometric Auto Tracking Light Bulb Security Camera



Fire Warning



Heat Mapping



Path Tracking



360° x 90°
Auto Tracking



Facial
Recognition



Military Encryption
Protection



1920 x1080
Resolution



Infrared Night
Vision



SPECIFICATION

Model (Apollo)	ACR1501R23WH	Field of View (FOV)	85±5° (Diagonal)
Encryptions Technologies	256-bit	Digital Zoom	4x
Privacy Protection	Yes	Pan / Tilt	Pan: -170° ~ 170° / Tilt: -20° ~ 10°
Wireless	Embedded Wi-Fi (2.4G) 802.11 b/g/n	Frame Rate	1920 x 1080 up to 30 fps
Multiple Wi-Fi Access Points	Connect up to 4 Wi-Fi Networks	Resolution	2M Pixels FHD
In-Ceiling	E26 or E27 Light Bulb Base	Streaming Quality	Automatically Adjusted
Light Lamp	Yes	Video Compression	H.264
Snapshot / Text / Offline Alert	Yes	Video Resolution	1080p, 720p, 480p, 360p
10-Second Video Alert	Yes ¹	Image Sensor	1/2.7" CMOS
Audio	Built-in Speaker and Microphone	IR / Flash LEDs	IR LEDs: 8, Flash LEDs: 6
Real-Time Two-Way Communication	Yes	MIMO Antenna	Embedded 2 x 2
Greetings Function	Yes	Local Storage	Supports up to 128GB Micro SD Card
Motion / Audio Detection	Yes	App Support	Amaryllo
Fire Warning	Yes ²	Mobile OS Requirements	iOS: 10.0 and up / Android: 5.0 and up
Human Detection	Yes ²	Google Services Connection	Yes
Vehicle Detection	Yes ²	PC Browser Support	Chrome / Firefox
Face Detection	Yes	Network Protocol	TCP/IP, UDP/IP, HTTP/HTTPS, DHCP, NTP, WPS
Pet Detection	Yes ²	NAS Support	SMB / CIFS
Day / Night Vision	Yes	Power Consumption	100V ~ 240V (5V / 2A DC)
Intruder Warning Light / Alarm	Yes	Dimensions (H x W x D)	10 x 10 x 26.7 cm / 3.94"x 3.94"x 10.51"
Multiple Viewers Support	Yes	Weight	502 g / 1.1 lb
Auto-Tracking Range	360°	Ambient Operating Temperature	32°F ~ 95°F / 0°C ~ 35°C
Activity / Blockout Zones	Max: 4	Warranty	One-Year Part Warranty

¹ Feature available under our Basic plan and above.

² Features available under our Plus plans and above.

Zeus

ACCESSORIES



Screw

