



PROPERTIES

COLOR: Off-White

APPLICATION CONSISTENCY: Brush, spray, or palm

AVERAGE WEIGHT/U.S. GALLON (ASTM D 1475):
10.5 lbs. (1.26 kg/l)

AVERAGE NON-VOLATILE (ASTM D 1644):
41.5% by volume

COVERAGE RANGE (FSTM 71):
(Subject to the type of surface being coated.)
Wet coverages shown below are for smooth non-porous surfaces. Porous or rough textured surfaces will require higher gallonage to obtain required dry thickness.

As An Encapsulant

Dry Thickness: 0.025 inch (0.64mm)
Equivalent Wet Coverage: 0.06 inch (1.52 mm)
3.7 gal./100 sq. ft. (1.5 l/m²)

As A Lockdown

400 sq. ft./gal. (9.8 m²/liter)

ODOR: Mild when wet; none when dry.

SERVICE TEMPERATURE LIMITS (FSTM 70):
(Temperature at coated surface of encapsulated ACM)
0°F to 170°F (-18°C to 77°F)

WET FLAMMABILITY (ASTM D 3278):
No Flash to Boiling (210°F/99°C)

SURFACE BURNING CHARACTERISTICS (ASTM E 84):

Flame Spread: 11
Smoke Developed: 2

Applied to 1/4 inch (6.4 mm) inorganic reinforced cement board at a coverage rate of 3 gallons/100 sq. ft. (1.22 liters/m²). The flame spread may vary at different product thicknesses and/or when applied over other surfaces.

[™] Trademark of Specialty Construction Brands, Inc.

Visit us on the web at www.fosterproducts.com

FOSTER[®] BRIDGING MASTIC ENCAPSULANT-LOCKDOWN

Foster[®] Bridging Mastic is a quality, dual-purpose coating designed specifically for the asbestos abatement industry.

Bridging Mastic is a field proven bridging encapsulant. Upon cure, 32-80 forms a tough, light colored, washable, abrasion resistant, elastomeric coating that economically abates the release of asbestos fibers from both conventional and spray applied asbestos-containing materials (ACM). Used with glass cloth, 32-80 is ideal for use over interior pipe covering and boiler lagging insulations.

Bridging Mastic can be diluted a maximum of 1:1 (water to 32-80) to produce an extremely effective lockdown (post-removal residual encapsulant). Applied at 400 sq. ft./gal., 32-80 cures to form a visible film effectively abating the release of remaining fibers.

BRIDGING MASTIC meets the requirements of NFPA 90A and 90B.

Meets requirements for LEED IEQ 4.2 Low-Emitting Materials, Paints and Coatings. VOC: 41 g/l, less water and exempt solvents.

LIMITATIONS

Protect from freezing until dry.
Not recommended for exterior use; select CP-211 instead.

Do not store or apply below 40°F (4°C) or above 100°F (38°C). As a lockdown, do not apply to surfaces in excess of 170°F (93.3°C).

Not suggested for use on floors.

APPLICATION GUIDE FOR FOSTER® BRIDGING MASTIC ENCAPSULANT - LOCKDOWN 32-80™

MATERIAL PREPARATION

Stir well but do not use sticks, boards, or anything else that could otherwise contaminate the product. DO NOT THIN. Dilute a maximum of 1:1 water: Foster® 32-80™ only when used as a lockdown.

SITE PREPARATION

As a minimum, follow all procedures outlined by Federal, State, and Local Authorities regulating asbestos abatement projects and the wastes generated therein.

MATRIX EVALUATION

Every ACM contemplated for encapsulation must be evaluated as to its inherent adhesive/cohesive strengths as well as its physical ability to receive an encapsulant. For further recommendations, contact your Foster representative.

APPLICATIONS

TO SPRAY APPLIED ASBESTOS CONTAINING MATERIALS - Using the recommended spray equipment, coat the matrix with Foster Bridging Mastic, holding the spray gun perpendicular to the surface of the ACM with the tip of the gun between 12 and 18 inches (30-46 cm) from the surface to be coated. Apply sufficient Foster 32-80 encapsulant to produce approximately one half the total recommended dry film thickness (minimum 25 mils wet). Allowing an open time of 8 hours (depending on the temperature and humidity conditions), a second application of encapsulant is made to the same area in the same manner, in an opposite pass direction from that used to apply the first coat. This procedure is continued until the total desired minimum dry film thickness is achieved.

TO PIPE COVERING AND BOILER LAGGING SYSTEMS - Clean the surface of the pipe covering/boiler lagging using a rag or sponge thoroughly moistened with Foster® Protektor® Sealant 32-22™. (In the case of a larger structure, spray apply a mist coat.) Consider the wipe pad to be contaminated material and dispose of in an appropriate manner. Coat the ACM with Foster Bridging Mastic via brush/spray to a minimum thickness of 25-30 mils wet. Imbed into this wet film a reinforcing membrane, smoothing out any wrinkles and overlapping all edges and seams at least 2 inches (5cm). (The reinforcing membrane should have weave openings no smaller than 10x10.) While the coating is still wet, apply a second coat of Foster Bridging Mastic in the same manner as the first. The resultant cured film shall have a minimum thickness of 25 mils dry.

IMPORTANT NOTE: The quantity of material required to properly encapsulate an ACM is a variable which is dependent upon the surface profile of the intended matrix. The estimated quantity required should be derived from a coverage test and equated to the larger area. The best means of insuring adequate coverage is to determine the amount of material that will be required for a specific area, segregate that quantity in the defined area, and apply until the segregated material is exhausted.

As a lockdown. Dilute Foster 32-80 a maximum of 1:1 (one part water to one part Foster 32-80). Insure that the dilution process does not introduce foreign particles or contaminants that could impair the bond of the applied material or efficiency of the application equipment. Keep the diluted product stirred to prevent settling.

APPROPRIATE SPRAY EQUIPMENT

Any of the following GRACO pumps (or their equivalent) can be used to spray Foster Bridging Mastic.

Pumps: Ultra Max 1095 or 1595

Hose: 3/8 inch (9.53mm) inside diameter minimum up to 100 lineal feet 1/2" (30M). 1/2" (12.7mm) diameter minimum for length beyond 100 lineal feet.

Gun: GRACO Silver or Golden Hydramastic gun with Reverse-A-Clean tip assembly.

Tip Size: .021" to .031" (0.53 to 0.79mm). Fan size is usually 4 to 6.

Average Viscosity: 60,000 - 80,000 cps.

CLEAN UP

Use fresh water to clean equipment before product dries. Dry product may be removed with hot soapy water or strong solvents such as chlorinated solvent (non-flammable) or xylol (flammable).



CUSTOMER SERVICE—800-231-9541 OR 800-338-2975

IMPORTANT: Specialty Construction Brands, Inc. warrants that each of its products will be manufactured in accordance with the specifications in effect on the date of manufacture. WE MAKE NO OTHER WARRANTIES AND EXPRESSLY DISCLAIM ANY WARRANTIES OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If a product fails to meet this limited warranty, purchaser's sole and exclusive remedy is replacement of the product or, at our option, refund of the purchase price. OUR ACCEPTANCE OF ANY ORDERS FOR THE PRODUCT IS EXPRESSLY CONDITIONAL UPON PURCHASER'S ASSENT TO THE TERMS ON THE APPLICABLE INVOICE.

ADEQUATE TESTS: The information contained herein we believe is correct to the best of our knowledge and tests. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be performed by you to determine if this product meets all of your requirements. The warranted shelf life of our products is six months from date of shipment to the original purchaser.

**For professional use only. Keep out of reach of children.
Consult Material Safety Data Sheet and container label for further information.**