



ISO-9001 Registered Quality System.
ISO-21469 Compliant.

Sales, Service & Distribution Center
Newark, NJ 07105
Phone: 973-589-9150 Fax: 973-589-4432

Manufacturing, Sales, Service & Distribution Center
Toledo, OH 43605
Phone: 419-691-2491 Fax: 419-693-3806

Sales and Tech Service Support
Phone: 1-800-733-4755

PRODUCT DATA

LUBRIPLATE LTR-2

DESCRIPTION

LUBRIPLATE LTR-2 is a red lithium complex grease that can be used for a variety of industrial, automotive and heavy-duty construction applications. This rugged, extreme pressure lubricant can withstand higher operating temperatures than traditional lithium multi-purpose greases as well as most lithium complex greases.

ADVANTAGES

LUBRIPLATE LTR-2 is tacky adhesive and very water resistant. The film strength and shear stability of this product is exceptional resulting in wear reduction and long lubricant life.

APPLICATIONS

LUBRIPLATE LTR-2 provides outstanding lubrication in a variety of applications including:

- ⇒ Automotive (including the fleet and truck operator)
- ⇒ Marine
- ⇒ Construction
- ⇒ Logging
- ⇒ Mining
- ⇒ Industrial

Typical Test Data

PROPERTY	TEST METHOD	TYPICAL RESULTS*
NLGI Grade	ASTM D-217	2
Type of Base		Lithium Complex
Appearance	Visual	Tacky, Red, Smooth
Dropping Point	ASTM D-2265	505°F/263°C
Kinematic Viscosity @ 40°C	ASTM D-445	460 cSt
Kinematic Viscosity @ 100°C	ASTM D-445	31 cSt
4-Ball EP Test - OK Load	ASTM D-2596	620 kg.
Water Washout @ 175°F	ASTM D-1264	< 5%
Corrosion - 3 hours	ASTM D-130	1a
4-Ball Wear	ASTM D-2266	0.52 mm
ISO VG	ASTM D-2422	460
Oil Separation	ASTM D-1742	0.11% by weight
Bearing Corrosion	ASTM D-1743	Pass – No Corrosion

PACKAGING AVAILABLE

Part No.

35 lb. Pail	L0167-035
120 lb. Quarter Size, Drum	L0167-039
400 lb. Full Size, Drum	L0167-040
Carton, 40/13.5 oz. Cartridges	L0167-098

