

Submittal Data Sheet SD118	EFFECTIVE 4/1/18
---	-----------------------------

SUBMITTAL DATA APPROVAL

For: _____

Job: _____

Date Submitted: _____ By: _____

Date Approved: _____ By: _____

Model Number: _____ Quantity: _____

Model Number: _____ Quantity: _____

Model Number: _____ Quantity: _____

Model Number: _____ Quantity: _____



- **Stainless Steel**
- **115V – 60Hz**
- **30psi Pressure Booster**
- **Automatically activates when water is drawn at a fixture**

US ASSEMBLY • 100% TESTED

Aqua-Max APB 30

Materials of Construction


- ShaftStainless Steel
- Impellers and Diffuser Chambers..... Stainless Steel
- Motor Bracket and Housing Aluminum
- Mechanical Seal.....Carbon/Carbide
- ControlComposite

The **AquaMotion APB 30** is designed to increase water pressure in a home by approximately 30 psi over the incoming water pressure to the home. The incoming pressure is either the pressure supplied by the municipality on the main to the home or the pressure developed by the homes water well system.

Specifications

- Maximum Shut-off Head: 77 Feet
- Maximum Flow: 28 GPM
- Maximum Operating Pressure: 145 psi (10 bar)
- Maximum Water Temp: 130°F (54°C)
- Weight 27 lbs. (11.34 Kg)

AquaMotion APB - 30



Dimensions

